



UP50-W

50 mm Ø, 5 mW – 85 W, 100 kW/cm²



KEY FEATURES

- 1. MODULAR CONCEPT**
Increase the power capability of your detector:
4 different cooling modules
- 2. VERY HIGH DAMAGE THRESHOLD**
100 kW/cm² in average power density
- 3. VERY LARGE APERTURE**
50 mm Ø effective aperture, perfect for the largest beams
- 4. HIGHEST ENERGY READINGS IN THE SERIES**
Measure single shot energy up to 500 J
- 5. SMART INTERFACE**
Containing all the calibration data

- 6. integra OPTIONS**
 - Standard: USB Output (-INT)
 - In Option: RS-232 Output (-IDR)

AVAILABLE MODELS



UP50N-40S-W9
(40W-Standalone)



UP50N-50H-W9
(50W-Heatsink)



UP50N-50F-W9
(50W-Fan-Cooled)



UP50M-50W-W9
(50W-Water-Cooled)

ACCESSORIES



Stand with Steel Post
(Model Number: 200234)



Extension Cables
(4, 15, 20 or 25 m)



Fiber Adaptors and Connectors
(FC, SC or SMA)



3-Port Fiber Cylinder with
Adaptors and Plug



12V Power Supply
(Model Number: 200130)



Pelican Carrying Case

SEE ALSO

HOW IT WORKS	14
CALIBRATION	6
TECHNICAL DRAWINGS	96
ABSORPTION CURVES	100
OEM DETECTORS	148
COMPATIBLE MONITORS	
MAESTRO	20
TUNER	24
UNO	26
S-LINK	28
P-LINK	30
M-LINK	32
LIST OF ALL ACCESSORIES	198
APPLICATION NOTE	
MEASURING LASER POWER WITH A THERMOPILE DETECTOR: THE BASICS!	202175
MEASURING HIGH POWER WITH A LOW POWER DETECTOR	202188

MONITORS

ENERGY DETECTORS

POWER DETECTORS

HIGH POWER SOLUTIONS

PHOTO DETECTORS

THZ DETECTORS

OEM DETECTORS

SPECIAL PRODUCTS

BEAM DIAGNOSTICS

UP50-W



*Also traceable to NRC-CNRC

SPECIFICATIONS

	UP50N-40S-W9	UP50N-50H-W9	UP50N-50F-W9	UP50M-50W-W9
MAX AVERAGE POWER (CONTINUOUS / 1 MINUTE)	40 W / 80 W	50 W / 85 W	50 W / 85 W	50 W ^f / 85 W ^f
EFFECTIVE APERTURE	50 mm Ø	50 mm Ø	50 mm Ø	50 mm Ø
COOLING METHOD	Convection	Heatsink	Fan-Cooled	Water-Cooled
MEASUREMENT CAPABILITY				
Spectral Range *	0.19 – 10.0 µm	0.19 – 10.0 µm	0.19 – 10.0 µm	0.19 – 10.0 µm
Noise Equivalent Power ^a	5 mW	5 mW	5 mW	5 mW
Rise Time (nominal) ^b	3.5 sec	3.5 sec	3.5 sec	3.5 sec
Sensitivity (typ into 100 kΩ load) ^c	0.12 mV/W	0.12 mV/W	0.12 mV/W	0.12 mV/W
Calibration Uncertainty ^d	±2.5 %	±2.5 %	±2.5 %	±2.5 %
Repeatability	±0.5 %	±0.5 %	±0.5 %	±0.5 %
Energy Mode				
Sensitivity	0.02 mV/J	0.02 mV/J	0.02 mV/J	0.02 mV/J
Maximum Measurable Energy ^e	500 J	500 J	500 J	500 J
Noise Equivalent Energy ^a	0.25 J	0.25 J	0.25 J	0.25 J
Minimum Repetition Period	11.1 sec	11.1 sec	11.1 sec	11.1 sec
Maximum Pulse Width	467 ms	467 ms	467 ms	467 ms
Accuracy with energy calibration option	±5 %	±5 %	±5 %	±5 %
DAMAGE THRESHOLDS				
Maximum Average Power Density ^g	100 kW/cm ²	100 kW/cm ²	100 kW/cm ²	100 kW/cm ²
Pulsed Laser Damage Thresholds	Max Energy Density		Peak Power Density	
1064 nm, 150 µs, 5 Hz	100 J/cm ²		667 kW/cm ²	
1064 nm, 7 ns, 10 Hz	1.1 J/cm ²		157 MW/cm ²	
532 nm, 7 ns, 10 Hz	1.1 J/cm ²		157 MW/cm ²	
248 nm, 26 ns, 10 Hz	0.7 J/cm ²		27 MW/cm ²	
PHYSICAL CHARACTERISTICS				
Effective Aperture	50 mm Ø	50 mm Ø	50 mm Ø	50 mm Ø
Absorber (High Damage Threshold)	W9	W9	W9	W9
Dimensions	89H x 89W x 32D mm	89H x 89W x 106D mm	89H x 89W x 116D mm	89H x 89W x 40D mm
Weight (head only)	0.62 g	0.93 g	1.38 g	0.81 g
ORDERING INFORMATION				
Product Name	UP50N-40S-W9-D0	UP50N-50H-W9-D0	UP50N-50F-W9-D0	UP50M-50W-W9-D0
Product Number (without stand)	200893	200884	200894	201886
Add Extension for INTEGRA (USB)	-INT	-INT	-INT	-INT
Product Number (without stand)	203059	203061	203063	203065
Add Extension for INTEGRA (RS-232)	-IDR	-IDR	-IDR	-IDR
Add Extension for BLU	-BLU	-BLU	-BLU	-BLU
Product Number (without stand)	203676	203679	203685	203682

Specifications are subject to change without notice // Compatible stand: P/N 200234

* For the calibrated spectral range, see the user manual.

a. Nominal value, actual value depends on electrical noise in the measurement system.

b. With anticipation.

c. Maximum output voltage = sensitivity x maximum power.

d. Including linearity with power.

e. For 360 µs pulses. Higher pulse energy possible when customized for long pulses (ms), less for short pulses (ns).

f. Minimum cooling flow 0.5 liters/min, water temperature ≤ 22°C, 1/8 NPT compression fittings for 1/4 incl semi-rigid tube.

Contact Gentec-EO for clean deionized water cooling module option.

g. At 1064 nm, 10 W CW.